

Skin Shape RF

Fractional Micro-Needles & Quadro Polar Technologies

SKIN SHAPE RF is an innovative product, designed to achieve:

- Skin Rejuvenation
- Body Contouring
- Facial Wrinkle removal
- Cellulite Improvement

INNOVATIVE TECHNOLOGY:

- **Temperature Sensors** integrated in the Applicators for continuous skin-temperature monitoring, assuring effective and problem free treatments
- **Fractional Micro-Needles** for effective and deep Skin Rejuvenation and Facial Wrinkle Removal.
- **Quadro & Bi-Polar Applicators:** Large working surface, with exact layer and deep tissue targeting
- **High Power** (up to 250 W_p) enabling a powerful treatment with the best possible results




On-Line Skin
Temperature
Measurement



Skin Shape RF



The Safe Method for Facial & Body Contouring

Bi-Polar
Temp. Controlled
Facial Applicator



• Deep Energy •
Penetration


Quadro-Polar
Temp. Controlled
Body Applicator



Physiological Process

Twisted & unsupportive
Collagen Fibers


Visible Wrinkle



Excessive layer of
Enlarged Fat Cells

Sorted & supportive
Collagen Fibers

Flattened Wrinkle



Reduced layer of
Normal Fat Cells

Skin Shape RF

The Safe Method for Facial & Body Contouring

Fractional RF with Disposable **Micro-Needles** 6x6 Heads


A built-in Fractional Handpiece with a selection of 3 types of Micro Needles Heads (0.5, 1.0 and 1.5 mm), is the perfect tool for Facial Skin rejuvenation and Fine Wrinkle Removal. The tiny "Holes" are triggering the skin to heal the "damage" by replacing cells and generating Collagen Fibers.



During RF Emission



After Removing Needles



Before



After 2 Treatments

Skin Shape RF

The Safe Method for Facial & Body Contouring



3 Simple Steps Operation:

- Set the Time **Duration**
- Set the recommended **Energy**
- Set the targeted Skin **Temperature**



MAXIMUM OUTPUT	250 W _P (100W RMS)
FREQUENCY	6.8 MHZ
APPLICATORS	BODY QUADRO POLAR AND FACIAL BI-POLAR FACIAL MICRO-NEEDLES BI-POLAR
TEMPERATURE SENSOR	INFRA-RED HI-SPEED INTEGRATED TEMPERATURE SENSOR IN EACH APPLICATOR
EMERGENCY HALTING	PATIENT'S EMERGENCY HALTING KNOB
MAINS	220-230VAC 50/60Hz 100-120VAC 50/60Hz
MAX MAINS POWER	600 VA